XT SERIES

Electrode Steam Humidifier



Electrode Steam Humidifier

- Easy to operate and maintain
- Adaptable
- Comprehensive Vapor-logic® controls



OST-EFFECTIVE STEAM HUMIDIFICATION



XT SERIES ELECTRODE HUMIDIFIER

XT Series electrode humidifiers use heat caused by electrical resistance in conductive fill water to boil the water into steam. Automatic draining and filling optimize humidifier performance according to your specific water type.

XT Series electrode steam humidifiers from DriSteem provide humidification for a wide range of buildings, including health care, commercial, industrial, and government facilities. Easy installation and minimal maintenance make XT Series one of the most affordable humidification systems to purchase and install.

EASY TO MAINTAIN

No cleaning required. Just replace the affordable steam cylinder when prompted by the controller display. The housing and painted doors resist corrosion. Model XTP housing is stainless steel.

ADAPTABLE

- · Compact in size to fit into small spaces, with attractive cabinet for finishedspace applications
- Model XTP capacity range is 2 to 130 kg/h
- Disperses steam into ductwork or open spaces
- Works with water conductivity from 350 to 1250 μS/cm
- User-selectable drain water tempering, if desired

COMPREHENSIVE CONTROL WITH VAPOR-LOGIC OPTION

Vapor-logic sets the standard for controller capabilities in electrode humidifiers.



Vapor-logic controller

Easy-to-use	√	
Web interfe	✓	
Accurate, r	✓	
Modbus® c inter-opera	✓	
Automatic based on v	✓	
Cylinder di	√	
USB port	For downloading controller data to a PC for viewing and analysis	√
	For data backup and restore	√
	For firmware updates	✓

Table 3-1: XT Series humidifier models, capacities, and electrical specifications

Model	Input power No	Nominal steam capacity	Nominal current draw (amps) *		
			Single	-phase	Three-phase
XTP	kW	kg/h	230V	400V	400V
002	1.7	2	7	_	_
003	3.3	5	15	8	5
006	6.0	8	26	15	9
010	10.0	14	_	_	14
017	16.5	22	_	_	24
025	25.0	34	_	_	36
033	33.3	45	_	_	48
042	41.7	57	_	_	60
048	47.8	65	_	_	69
050	50.0	68	_	_	2 x 36
067	66.7	90	_	_	2 x 48
083	83.3	113	_	_	2 x 60
096	95.7	130	_	_	2 x 69

^{*} For circuit protection requirements, see the XT Series Humidifier Installation, Operation, and Maintenance Manual (IOM), available at www.dristeem.com.

Table 3-2: Dimensions by model number								
	Model XTP							
Description	002, 003, 006	010, 017	025, 033, 042, 048	050*, 067*, 083*, 096*				
	mm	mm	mm	mm				
Width	370	450	504	1005				
Height	523	612	650	650				
Depth	221	300	340	340				



No cleaning required. Just replace the affordable steam cylinder when prompted.

Insert a USB flash drive into the USB port on the controller board to perform firmware updates or to back up and restore data.



DriSteem Corporation

A subsidiary of Research Products Corporation DriSteem U.S. operations are ISO 9001: 2015 certified.

U.S. Headquarters: 14949 Technology Drive Eden Prairie, MN 55344 800-328-4447 or 952-949-2415 952-229-3200 (fax)

Continuous product improvement is a policy of DriSteem Corporation; therefore, product features and specifications are subject to change without notice.

DriSteem and Vapor-logic are registered trademarks of Research Products Corporation and are filed for trademark registration in Canada and the European community.

Product and corporate names used in this document may be trademarks or registered trademarks. They are used for explanation only without intent to infringe.

© 2022 Research Products Corporation





Form No. XT-BRO-M-2022-0122

EXPECT QUALITY FROM THE INDUSTRY LEADER

For more than 45 years, DriSteem has been leading the industry with creative and reliable humidification solutions. Our focus on quality is evident in the construction of the XT Series humidifier. DriSteem leads the industry with a Two-year Limited Warranty and optional extended warranty.

For more information www.dristeem.com sales@dristeem.com

For the most recent product information visit our website: www.dristeem.com