


# BACnet HUMIDISTAT EXTERNAL CONTROL CONNECTIONS DIAGRAM

DATE	REV	RECORD	DR
9/22	A	E.C.# 7110	JK
8/23	B	E.C.# 7173	JK
2/24	C	E.C.# 7229	JK



**NOTES:**

- ① FOR ALL CONTROL DEVICES. 18 AWG/1.5 mm<sup>2</sup> PLENUM RATED 2-WIRE SHIELDED CABLE.
- ② SEE VLV DRAWING FOR VALVE SPECIFIC WIRING.
- ③ WITH VAPOR-LOGIC, CONNECT ALL SAFETIES TO VL AND JUMPER ALARM INPUTS AT HUMIDISTAT.
- ④ USE LARGE WIRE NUT OR EQUIVALENT TO CONNECT ALL GROUNDS.

<b>BACnet HUMIDISTAT CONNECTIONS WIRING DIAGRAM</b>	
	MAT'L: SCALE: DRAWN BY: JK DATE: 9/14/22
P/N BAC-1	